Data Sheet



Coaxial Cable Connector 11_SMB-50-1-40/111_N

Description

Straight cable plug

Interface standards
IEC 60169-10_MIL-STD-348A/311_CECC 22130



Technical Data

Electrical Data

 $\begin{array}{ll} \text{Impedance} & 50 \ \Omega \\ \text{Interface frequency max.} & 4 \ \text{GHz} \end{array}$

Mechanical Data

Centre contact crimped
Outer contact crimped
Weight 0.0024 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102) -65 °C to 165 °C compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Related Documents

Outline drawing DOU-00006511
Catalogue drawing DOU-00006508
Assembly instruction DOC-0000179013

Ordering Information

Bulk 100 pcs package 11_SMB-50-1-40/111_NH Single package 11_SMB-50-1-40/111_NE

Additional Information

Suitable cables RG_178_B/U, ENVIROFLEX_178, RG_196_A/U

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.