## Product Datasheet GU10 Halogen Lamps



Туре	Beam Angle	Voltage	Wattage	Colour	Life
		$(\vee)$	(VV)	Rating	(Hours)
GU10/GZ10	40	220-240	20	2800k	2,000
GU10/GZ10	40	220-240	25	2800k	2,000
GU10/GZ10	40	220-240	35	2800k	2,000
GU10/GZ10	40	220-240	40	2800k	2,000
GU10/GZ10	40	220-240	50	2800k	2,000
GU10/GZ10	40	220-240	75	2800k	2,000

Available as in a variety of power and beam angle variants with ex-stock availability for:

Code	Description
GU10H20WCL	GU10 Halogen lamp 20W 230V Clear
GU10H35WCL	GU10 Halogen lamp 35W 230V Clear
GU10H50WCL	GU10 Halogen lamp 50W 230V Clear

## Features

- Lamp life up to 2,000 hours
- Aluminium coated reflector
- Manufactured under ISO9000
- CE Approved and RoHS Compliant