

MkIII Industrial Safety Helmet

Conformity:

Conforms to BS EN 397.

EC Certificate Number 0279,
issued by BSI Product Certification.

- Low dome profile
- Helmet offers electrical insulation
- Incorporates a rain channel
- Available in a wide choice of colours
- Company personalisation available by printing
- Compatible with other JSP safety products

Size & Weights:

530-620mm (6½ - 7⅞)

Poly or Webbing Harness - 0.35Kg

Wheel Ratchet Harness - 0.38Kg

(Weight is approx.)

Materials:

Shell - HDPE

Webbing Harness - LDPE Strap

LLDPE Harness Clips

Terylene Webbing Straps

Brushed Nylon Backed Foam Sweatband

Wheel Ratchet Harness - LDPE Strap

LLDPE Harness Clips

Nylon Ratchet Assembly With Steel Screw & Washer

Terylene Webbing Straps

Brushed Nylon Backed Foam Sweatband

Instructions For Use:

Fit helmet on head and fasten strap to ensure correct fit. For adequate protection this helmet must be worn with the peak facing forward and adjusted to the size of the users head.

Limitations Of Use:

Protection will only be offered if the helmet is fitted correctly. Any helmet subjected to a severe impact should be replaced immediately. Do not apply paint, solvents, adhesives or self-adhesive labels, except in accordance with instructions from the manufacturer. The harness, when in contact with the skin may cause allergic reactions to susceptible individuals. If this occurs leave the hazard area, remove the cap and seek medical advice.

Cleaning & Maintenance:

The helmet may be cleaned with soap and warm water and dried with a soft cloth. Chemical or abrasive cleaners should not be used. The cover can be brushed clean with a stiff brush. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.