

Coaxial Cable Connector 16_MBX-50-2-1/113_N

Description

Right angle cable plug

Interface standards
HUBER+SUHNER MBX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Centre contact soldered
Outer contact crimped
Weight 0.002888 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Bronze / Brass	SUCOPRO Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing DOU-00162035
Catalogue drawing DCA-00161645
Assembly instruction DOC-0000326568

Ordering Information

Single package 16_MBX-50-2-1/113_NE

Additional Information

Suitable cables ENVIROFLEX_316_D, K_02252_D, G_02232_D