

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2149202221](#)
Status: **Active**
Overview: [Off-the-Shelf Pre-Crimped Leads](#)
Description: Pre-Crimped Lead PicoBlade Female-to-PicoBlade Female, Gold Plated, 75.00mm Length, 26 AWG, Red

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family Cable Assemblies
Series [214920](#)
Assembly Configuration Pre-crimped Lead Only
Connector to Connector PicoBlade Crimp Terminals
Overview [Off-the-Shelf Pre-Crimped Leads](#)
Product Name PicoBlade
UPC 193264502523

Physical

Cable Length 75.00mm
Circuits (Loaded) 1
Color - Resin Red
Gender Female-Female
Material - Metal Phosphor Bronze
Material - Plating Mating Gold
Material - Plating Termination Tin
Net Weight 0.206/g
Packaging Type Bag
Pitch - Mating Interface 1.25mm
Plating min - Mating 0.380µm
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.04mm max.
Wire Size AWG 26
Wire/Cable Type UL 1061

Electrical

Current - Maximum per Contact 1.0A
Voltage - Maximum 125V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Sales Drawing 2149202221-000



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[214920](#) Series

Use With

[51021](#) PicoBlade Crimp Housing