Surface-mounted luminaire LINURA.edge - LEA 600/850/S

114035000-00801346



ENGINEER OF LIGHT.

Energy efficiency category A/A+/A++



light source

work equipment connected load Power consumption luminous flux luminous efficacy light distribution

colour temperature color rendering index (CRI)

glare control System of protection class of protection technology operation luminaire body

lamp cover

weight (net) approx. 0.2 kg, (0.44 lb) mains supply design

Fastening dimension 22-26 V; DC approx. 6 W approx. 630 lm approx. 105 lm/W direct neutral white, approx. 5000 K > 80 screen IP54 Ш switchable external aluminium/plastic, anodised; painted, aluminium coloured

without

anodised Acrylic satine

built-in plug M12-A-5 mounted version bracket

A=335mm, C=290mm, C1=320mm A=13.18in, C=11.41in, C1=12.59in









M12-A-5

illuminance

luminous intensity





