Expandable Sleeving



RoHS Compliant



Features

- Rated to 125°C
- Low temperature flexibility to -70°C
- Can be cut with ordinary scissors, eliminates the need for hot-knife cutting
- · Does not trap heat or humidity
- Rot-tree
- Self-fitting over many shapes and sizes
- Self-extinguishing when used to encase typical non-flammable wires or cables

Note

This fray resistant sleeving should not be used in hard vacuum environments nor immersed in solvents or liquids where the fray resistant treatment particulates could contaminate the system environment.

Part Number Table

Description	Nominal Size	Minimum Diameter	Maximum Diameter	Typical Weight (lb/ft)	Spool Length (ft.)	Part Number
Expandable Sleeving, Fray Resistant, Black	1/8	3/32	1/4	0.0019	100	SPC12212
	1/4	1/8	7/16	0.0027		SPC12213
	3/8	1/4	1/2	0.0058		SPC12214
	1/2	1/4	3/4	0.0078		SPC12215
	3/4	1/2	1 1/4	0.013	50	SPC12216
	1 1/4	3/4	1 3/4	0.0168		SPC12217
	1 3/4	1 1/4	2 3/4	0.0272	25	SPC12218
	2	1 1/2	3 1/2	0.0332		SPC12219
	2 1/2	1 3/4	4 1/2	0.0462		SPC12220

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

