

Within Series Adaptor 34_N-75-0-1/133_N

Description

Bulkhead adaptor jack/jack
N jack (female) / N jack (female)

Interface standard
Series N - Not compatible to N 50 Ohms



Technical Data

Electrical Data

Impedance 75 Ω
Interface frequency max. 1.5 GHz

Mechanical Data

Number of matings 500
Weight 0.0464 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

Material Data

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

Related Documents

Catalogue drawing DCA-00013619

Ordering Information

Single package 34_N-75-0-1/133_NE