Data Sheet



Between Series Adaptor 33_NEX10-4310-50-X1/003_-

Description

Adaptor plug/jack

NEX10 plug (male) / 4.3-10 jack (female)

Interface standards
Series NEX10 - Standard
Series 4.3-10 - IEC 61169-54

Technical Data

Electrical Data

Impedance 50Ω

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102) -55 °C to 85 °C compliant

Material Data

Interface - NEX10 plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Silver Plating
Outer contact	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - 4.3-10 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Silver Plating
Outer contact	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	

Related Documents

Outline drawing DOU-00340180

Ordering Information

Single package 33_NEX10-4310-50-X1/003_-E

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.