5kV, 4mm Sheathed Banana Jack, Panel Mount, 4.8mm Quick Connect


CT4008-#



Features:

- 1,000 V CAT IV, 5 kV non-category with 2 kV transient overvoltage
- Ø4.8 mm Quick connect termination
- 10 A Max
- Panel mount
- CE listed
- · RoHS 2 compliant

Measurement Drawing: (dimensions in mm, not to scale)



Description:

The CT4008 operates up to 5 kV when used in non-category environments with transient overvoltages up to 2 kV.^a This jack also extends the rating of our 4mm Sheathed Banana Jacks to 1,000 V CAT IV.^b

For use only with Cal Test's Long-Reach High Voltage Test Leads, CT3018 or CT3020. The jack offers a Ø4.8 mm quick connect tab. The jack fits into both plastic and metal panels fixed with a 14.5 mm hex panel nut.

The CT4008 is available in 2 colors.

a. Never hold or touch equipment while connected to live voltages.b. Must be used in conjunction with other similarly rated products.



Specifications and appearance subject to change without notice D400800 020720

1 - www.caltestelectronics.com

Order Information:

CT4008-#

5kV, 4mm Sheathed Banana Jack, Panel Mount, 4.8mm Quick Connect

• Color: replace '-#' with dash number: •0 Black, -2 Red

Contact Info:

Toll Free: 800-572-1028 (US Only) Phone: 714-221-9330 Fax: 714-921-9849 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610 USA www.caltestelectronics.com

CE

Copyright © 2020, Cal Test Electronics, Inc. All rights reserved. Information in this publication supersedes that in all previously published material. Trade names referenced are the service marks, trademarks or registered trademarks of their respective companies.



Specifications and appearance subject to change without notice D400800 020720 2 - www.caltestelectronics.com