

## LP Xenon



CE – certified to EMC directive 89/336/EC.

Complies with low voltage directive 2006/95/EC.

High voltage transient and polarity reversal protected.

Operating temperature: -20°C to + 55°C.



| LP4XMV/2          | 75/min | single flash<br>(all beacons) | IP67<br>(all beacons) | 100gms<br>(1/2W beacons) |
|-------------------|--------|-------------------------------|-----------------------|--------------------------|
| LP4XMV/5          |        |                               |                       | 110gms<br>(5W beacons)   |
| All other beacons | 60/min |                               |                       |                          |

### Features:

A range of 1W, 2W and 5W low profile Xenon beacons.

- Low current consumption
- Available in 12, 24, 110 and 230V versions
- Multivoltage option (10–100Vdc, 20–72Vac)
- Weatherproof to IP67
- 360° visibility
- 12 months' guarantee

### Mounting Options:

See LP-LED page for mounting options.

### Materials:

Polycarbonate lens and base. ROHS compliant.

| Description | Power | Voltage      | Voltage Range         | Current Consumption  | Clear  | Amber  | Red    | Blue   | Green  |
|-------------|-------|--------------|-----------------------|--|--------|--------|--------|--------|--------|
| LP1X12/1    | 1W    | 12Vdc        | 10-15vdc              | 115mA @ 12Vdc  | 412021 | 412022 | 412023 | 412024 | 412025 |
| LP1X24/1    | 1W    | 24Vdc        | 20-30Vdc              | 55mA @ 24Vdc   | 412031 | 412032 | 412033 | 412034 | 412035 |
| LP1XMV/1    | 1W    | Multivoltage | 10-100Vdc<br>20-72Vac | 112mA @ 12Vdc, 63mA @ 24Vdc<br>50mA @ 50Vac, 29mA @ 100Vac   | 412051 | 412052 | 412053 | 412054 | 412055 |
| LP1X12/2    | 2W    | 12Vdc        | 10-15vdc              | 220mA @ 12Vdc  | 440001 | 440002 | 440003 | 440004 | 440005 |
| LP1X24/2    | 2W    | 24Vdc        | 20-30Vdc              | 110mA @ 24Vdc  | 440021 | 440022 | 440023 | 440024 | 440025 |
| LP4XMV/2    | 2W    | Multivoltage | 10-100Vdc<br>20-72Vac | 130mA @ 12Vdc, 95mA @ 24Vdc<br>83mA @ 50Vac, 37mA @ 100Vac   | 412061 | 412062 | 412063 | 412064 | 412065 |
| LP4XMV/5    | 5W    | Multivoltage | 10-100Vdc<br>20-72Vac | 250mA @ 12Vdc, 200mA @ 24Vdc<br>112mA @ 50Vac, 60mA @ 100Vac | 412091 | 412092 | 412093 | 412094 | 412095 |
| LP1X110/2ac | 2W    | 110Vac       | 90-125Vac             | 100mA @ 110Vac   | 441001 | 441002 | 441003 | 441004 | 441005 |
| LP1X230/2ac | 2W    | 230Vac       | 207-253Vac            | 40mA @ 230Vac  | 441021 | 441022 | 441023 | 441024 | 441025 |

