

## LT Xenon







CE – certified to EMC directive 89/336/EC.

Complies with low voltage directive 2006/95/EC.

High voltage transient and polarity reversal protected.

Operating temperature: -20°C to + 55°C.



				
LT4XMV/2	75/min	single flash (all beacons)	IP67 (all beacons)	126gms (2W beacons)
LT4XMV/5				136gms (5W beacons)
All other beacons	90/min			

### Features:

A range of 2W and 5W compact Xenon beacons.

- Low current consumption
- Available in 12, 24, 110 and 230V versions
- Multivoltage option (10–100Vdc, 20–72Vac)
- Weatherproof to IP67
- 360° visibility
- 12 months' guarantee

### Mounting Options:

See LT–LED page for mounting options.

### Materials:

Polycarbonate lens and base. ROHS compliant.

Description	Power	Voltage	Voltage Range	Current Consumption	Clear	Amber	Red	Blue	Green
LT4XMV/2	2W	Multivoltage	10-100Vdc 20-72Vac	130mA @ 12Vdc, 95mA @ 24Vdc 83mA @ 50Vac, 37mA @ 100Vac	411061	411062	411063	411064	411065
LT4XMV/5	5W	Multivoltage	10-100Vdc 20-72Vac	255mA @ 12Vdc, 190mA @ 24Vdc 112mA @ 50Vac, 70mA @ 100Vac	411071	411072	411073	411074	411075
LT3X12/5	5W	12Vdc	10-15vdc	360mA @ 12Vdc	411021	411022	411023	411024	411025
LT3X24/5	5W	24Vdc	20-30Vdc	160mA @ 24Vdc	411041	411042	411043	411044	411045
LT3X110/5 ac	5W	110Vac	90-125Vac	50mA @ 110Vac	410021	410022	410023	410024	410025
LT3X230/5 ac	5W	230Vac	207-253Vac	40mA @ 230Vac	410001	410002	410003	410004	410005

