



Assembled Iron Conduit Bender 3/4-Inch EMT



This Assembled Conduit Bender features a wide foot pedal for comfort and stability. It is made of steel and can handle up to 3/4-Inch EMT. This bender comes with degree scales, multiplier scales, and center bend marks for accurate bends.

Specifications

Type:	Benfield® Head Iron Conduit Bender	Application:	Stub Ups, Offsets, Back-to-Back, Saddle Bends and Other Bends
Special Features:	Wide Foot Pedal for Stability, Leverage and Comfort	Overall Length:	36.45" (92.6 cm)
Overall Height:	2.52" (6.4 cm)	Overall Width:	9" (22.9 cm)
Material:	Steel	Handle Length:	38" (96.5 cm)
Centerline Bend Radius:	5" (13 cm)	Thinwall/EMT:	3/4" (1.9 cm)
Rigid/IMC:	0.5" (1.3 cm)	Marking:	Degree Scales, Multiplier Scales, Center Bend Marks
Included:	Handle 51427	Weight:	6.6 lb (3.0 kg)