



Pliers, Long Nose Side-Cutters, Insulated, 7-Inch



Klein Tools Insulated Long Nose Side-Cutting pliers are 1000V rated for safety on the job. The long nose is designed for grabbing and looping wire. Dual layer, orange-over-white insulation provides a warning sign that insulation may be compromised. The molded insulation meets or exceeds ASTM F1505-16 and IEC 60900:2012 standards for insulated tools. Cutting knives are induction hardened for long life.

Specifications

Type:	Long Nose Side Cutting Pliers	Application:	For Work Near Energized Sources
Special Features:	Flame Retardant and Impact Resistant Handle	Overall Length:	7.38" (18.7 cm)
Material:	Induction Hardened Steel	Jaw Length:	2.438" (6.2 cm)
Jaw Width:	0.688" (1.8 cm)	Jaw Thickness:	0.375" (1 cm)
Point Diameter:	.094" (2.4 mm)	Cutting Knives:	Standard
Knife Length:	0.5" (1.3 cm)	Cut Style:	Side-Cutting
Joint Type:	Hot-Riveted	Handle Color:	Orange
Handle Finish:	2-Layer	Insulated:	Yes
Standard:	IEC 60900 and ASTM F1505	Weight:	4.8 oz (136 g)