



Threadclip, Blunt Tips, 4-1/2-Inch



Spring Action opens automatically. Chrome over nickel plated. Blunt tips. 4-1/2 inches (114.3 mm) overall length; 1-3/8 inches (34.9 mm) cut length.

Specifications

Material:	Carbon Steel	Blade Curvature:	Straight
Blade Edge:	Standard	Blade Length:	1.375" (3.5 cm)
Blade Tip:	Blunt	Blade Finish:	Chrome Over Nickel Plated
Handed:	Right	Handle Material:	Metal
Handle Orientation:	Straight	Handled:	Right
Tension Adjustment:	Screw	Overall Length:	4.5" (11.4 cm)
Overall Height:	0.375" (1 cm)	Overall Width:	1.5" (3.8 cm)
Weight:	2.6 oz (73 g)		