



Parallel Jaw Grip 4600 Series



Lightweight, compact grips pull an exceptionally wide range of cable sizes and types. Designed with a round serrated jaw to firmly grip insulated cables and conductors. A hot latch closed automatically to guard against grip accidentally disengaging from wire. A large opening in the handle accommodates a wide variety of hooks on hoists, winches and tackle blocks.

Specifications

Type:	Parallel Jaw Grip	Application:	Firmly Grip Insulated Cables and Conductors
Special Features:	Spring	Overall Length:	13" (33 cm)
Overall Height:	1.5" (3.8 cm)	Overall Width:	5" (12.7 cm)
Cable Type:	ACSR	Cable Diameter:	0.3" to 0.8" (7.62 to 20.3 mm)
Hot Latch:	N	Swing Latch:	N
Spring:	Y	Locking Handle:	N
Jaw Type:	Round - Serrated	Jaw Length:	5" (12.7 cm)
Maximum Safe Load:	10,000 lb (4536 kg)	Weight:	7.0 lb (3.2 kg)