



Grip, Hot-Line Latch, Bare Cable .12 to .37-Inch



Specifications

Type:	Chicago Grip	Cable Type:	Aircraft, EHS, Messenger, Guy Strand
Cable Diameter:	0.12" to 0.37" (3.05 to 9.4 mm)	Hot Latch:	Y
Swing Latch:	N	Spring:	Y
Locking Handle:	Y	Jaw Type:	Double V
Jaw Length:	4.188" (10.6 cm)	Maximum Safe Load:	4500 lb (2041 kg)
Weight:	3.2 lb (1.4 kg)		