



PRODUCT-DETAILS

EGR3LS1-S32

REC LED SIGN M3 32M

General Information

Extended Product Type	EGR3LS1-S32
Product ID	7TCA091160R0362
EAN	5415022327496
Catalog Description	REC LED SIGN M3 32M
Long Description	Guideway 32M Recessed Luminaire, M3, 220-240 AC 50Hz, 1 LED 4W, Environment Temperature 5-35 Degrees Celsius, Includes Arrow Up and Blank Pictogram

Ordering

EAN	5415022327496
Customs Tariff Number	9405409100

Dimensions

Product Net Weight	3.11 lb 1.41 kg
--------------------	--------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1.61 in 41 mm
Package Level 2 Height	6.28 in

	160 mm
Package Level 2 Depth / Length	2.05 in
	52 mm

Additional Information

Battery Type	Industrial
Battery Chemical Composition	Nickel-Metal Hydride
Number of Batteries	1
Product Main Type	SELF CONTAINED LUMINAIRE
Product Name	EMERGENCY LIGHTING
UPC	075114244664

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	7TKK000717
Declaration of Conformity - CE	7TKK001139
Instructions and Manuals	7TKK000717

Classifications

ETIM 6	EC001957 - Emergency luminaire
ETIM 7	EC001957 - Emergency luminaire
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Emergency Lighting