

EG3LS1-S22



LED SIGN M3 22M



General Information

Extended Product Type	EG3LS1-S22
Product ID	7TCA091160R0359
EAN	5415022327229
Catalog Description	LED SIGN M3 22M
Long Description	Guideway 22M Surface Luminaire, M3, 220-240 AC 50Hz, 1 LED 2W, Environment Temperature 5-35 Degrees Celsius, Includes Arrow Up and Blank Pictogram
Number of Batteries	1

Ordering

EAN	5415022327229
Minimum Order Quantity	1 piece
Customs Tariff Number	9405408440

Dimensions

Product Net Width	1.61 in
Product Net Height	6.28 in
Product Net Depth / Length	2.05 in
Product Net Weight	1.111 kg

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	40.894 mm
Package Level 2 Height	159.512 mm
Package Level 2 Depth / Length	52.07 mm

Additional Information

Product Main Type	STANDARD EMERGENCY LIGHTING
Product Name	EMERGENCY LIGHTING
UPC	075114244176

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	EG3LS1-S22
Instructions and Manuals	EG3LS1-S22

Classifications

ETIM 6	EC001957 - Emergency luminaire
ETIM 7	EC001957 - Emergency luminaire
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Emergency Lighting

