

SR2-DEA-M3



REC M3 AUTOTST ESC-4MH WH



General Information

Extended Product Type	SR2-DEA-M3
Product ID	7TCA091160R0445
EAN	5415022292404
Catalog Description	REC M3 AUTOTST ESC-4MH WH
Long Description	Serenga 2 Escape Route, Recessed Luminaire, M3, 220-240 AC 50Hz, Lamp Type 1 LED 2 W, Lamp Output 203 Lumens, Environment Temperature 5-40 Degrees Celsius, Automatic Self Test, White
Number of Batteries	1

Ordering

EAN	5415022292404
Minimum Order Quantity	1 piece
Customs Tariff Number	9405408440

Dimensions

Product Net Width	6.5 in
Product Net Height	2.44 in
Product Net Depth / Length	8.74 in
Product Net Weight	0.581 kg

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	165.1 mm
Package Level 2 Height	61.976 mm
Package Level 2 Depth / Length	221.996 mm

Additional Information

Product Main Type	STANDARD EMERGENCY LIGHTING
Product Name	EMERGENCY LIGHTING
UPC	075114211925

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SR2-DEA-M3
Instructions and Manuals	SR2-DEA-M3

Classifications

ETIM 6	EC001957 - Emergency luminaire
ETIM 7	EC001957 - Emergency luminaire
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Emergency Lighting

