



MINI RGBW LED SPOT WITH DMX - 15W

MINICOLOR15

Compact-sized projector fitted with a 15W RGBW LED. Due to its small size, it is suitable for numerous applications such as illumination of Truss, small premises, etc.

- 7 DMX modes
- 1x 15W 4-in-1 RGBW Osram LED
- Beam angle 12°
- Aluminum case
- Heat sink
- 16bit dimmer
- Strobe
- Auto-static control

**EAN
CODE**

**5420047135377
16-2886**

SPECIFICATIONS TECHNIQUES

Power supply	100-240V~ 50/60Hz
Consumption	21W
Dimensions	212 x 120 x 80mm
Weight	1.01kg



LOGISTICS VALUES

Height	22.5 cm
Width	15.5 cm
Depth	8.5 cm
Volume	0.002964 m³
Net weight	1.1 kg
Packaging height	22.5 cm
Packaging width	15.5 cm
Packaging depth	8.5 cm
Packaging volume	0.003 m³
Packaging gross weight	1.21 kg
Master carton height	22.5 cm
Master carton width	15.5 cm
Master carton depth	8.5 cm
Master carton net weight	1.1 kg
Master carton gross weight	1.21 kg
Palette hauteur	0.41 cm
Palette largeur	0.8 cm
Palette profondeur	1.2 cm
Qty per packaging	1
Qty per master carton	1
nb uvc par palette	5
nb couches parpalette	1
nb cartons par couche	5
EAN14 code	54200471353778
Customs code	94054091

