
PRODUCT-DETAILS

HSMS 16C

HSMS16C Hosuemaster compact



General Information

Extended Product Type	HSMS 16C
Product ID	1SKB118142C4001
EAN	6221115048784
Catalog Description	HSMS16C Hosuemaster compact
Long Description	HSMS16C Housemaster compact consumer unit, Surface, cold roled sheet steel 1mm, steel flap, 1row, 16 way, with incomer Isolator E202-100A

Ordering

EAN	6221115048784
Minimum Order Quantity	1 piece
Customs Tariff Number	85389320

Dimensions

Product Net Width	368 mm
Product Net Height	256 mm
Product Net Depth / Length	110 mm

Container Information

Package Level 1 Units	1 piece
-----------------------	---------

Package Level 1 Width	368 mm
Package Level 1 Height	256 mm
Package Level 1 Depth / Length	110 mm
Package Level 1 Gross Weight	4.7 kg

Additional Information

Degree of Protection	IP30
Housing Material	Steel
Mounting Type	Surface mounted (plaster)
Number of Groups	1
Number of Phases	16
Number of Phases in Cooking Group	0
Number of Poles Main Switch	2
Product Main Type	HSMS
Product Name	consumer unit-Housemaster
Protection Type	Miniature- / earth leakage circuit breaker

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SKC802015C0203
Declaration of Conformity - CE	1SKC100819C0001
Instructions and Manuals	1SKC802015C0203

Classifications

ETIM 6	EC002288 - Small distribution board equipped
ETIM 7	EC002288 - Small distribution board equipped
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Enclosures → Consumer Units → Consumer Units

