productinformation

tesa® 4662

Strong duct tape

tesa® 4662 is a strong duct tape. It consists of a 27 mesh woven PET/cotton fabric backing coated with a natural rubber adhesive.

tesa® duct 4662 is a self adhesive tape with typical duct features for a wide range of applications.

Features:

- excellent adhesion even on rough and dusty surfaces (e.g. brickwork, timber)
- water repellent
- conformable

Main Application

- Sealing of pipes and ducts
- Bonding of construction and protection films
- Closing of covering foils
- Application on brickwork and timber
- Fixing, closing, packaging and a lot more!

Technical Data

٠	Backing material	PE laminated cloth	•	Elongation at break	18 %
•	Total thickness	230 μm	•	Tensile strength	30 N/cm
•	Type of adhesive	natural rubber	•	Temperature resistance (30 min)	95 °C
•	Adhesion to steel	4.4 N/cm	•	Mesh	27 count per square
					inch

Properties

	Hand tearability	• • •		Abrasion resistance	• •
•	Straight tear edges	•••	•	Water resistance	••

Evaluation across relevant tesa® assortment: ●●● very good ●●● good ●● medium ● low