

June, 2009

3M[™] Scotch[®] Strapping Tape 8898

Product Description

TΝ

Scotch® Strapping Tape 8898 is a general-purpose tape with a tensilized polypropylene film backing and pressure-sensitive synthetic adhesive. The tape is designed for a wide variety of industrial and packaging applications. Some typical applications include bundling, reinforcing, strapping, box closing, and appliance securing. The backing provides proper stiffness and excellent abrasion, moisture, and scuff resistance. The pressure-sensitive adhesive is specifically formulated to provide balanced adhesion to most fiberboard surfaces and a wide variety of plastic and metal surfaces. We suggest tests be completed to determine suitability particularly on surfaces other than those previously mentioned.





3M[™] Scotch[®] Strapping Tape 8898

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Property	Values		Method
Backing Color	Blue, Ivory		
Total Tape Thickness	0.12 mm	4.6 mil	ASTM D3652
Backing	Tensilized polypropylene		
Adhesive	Pressure-sensitive synthetic rubber resin		

Typical Performance Characteristics

180° Peel Adhesion		
8.2 N/cm	75 oz/in	82 N/100mm
Property: 180° Peel Adhesion Method: ASTM D3330 Dwell/Cure Time: 72 hr Substrate: Stainless Steel Backing: 2 mil Aluminum Foil notes: 12 in/min (305 mm/min)		

Tensile Strength		
280 N/cm	2800 N/100mm	160 lb/in

Property: Tensile Strength Method: ASTM D3759

Elongation at Break: 32 %

Methods

ASTM D3759

Storage and Shelf Life

Store behind present stock. Store in a clean, dry place. Temperature of 40-80°F (4-26°C) and 40-50% relative humidity are recommended. Rotate your stock. To obtain best performance, use this product within 18 months from date of manufacture.

Trademarks

Scotch is a registered trademark of 3M.

References

Property	Values
3m.com Product Page	https://www.3m.com/3M/en_US/company-us/all-3m-products/~/Scotch- Strapping-Tape-8898?N=5002385+3293242202&rt=rud
Safety Data Sheet (SDS)	https://www.3m.com/3M/en_US/company-us/SDS-search/results/? gsaAction=msdsSRA&msdsLocale=en_US&co=ptn&q=8898

ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



3M United States 3M Center St. Paul, MN 55144-1000 800-362-3550 www.3M.com