



62 Tape

Bondable PTFE Film

Data Sheet

Product Description

- 2.0-mil PTFE backing, supplied on a liner
- Silicone thermosetting adhesive
- Supplied on 3 inch cores

Like all 3M insulating tapes, 3M™ 62 Tape is available in standard and custom widths and lengths. Standard length is 36 yards.

- Widths from 1/4" to 14"
- Longer lengths up to several times normal length, dependent upon width. Check with Customer Service.

Applications

3M 62 Tape is supplied on a liner; bondable backside for higher adhesion to its own backing and better bonding of resins and varnishes; for use on high temperature coils, capacitors and wire harnesses. Printable.

Properties

Typical Values

Adhesive	Silicone Thermosetting
Backing	PTFE Film
Backing Thickness ¹	2.0 Mil
Total Thickness	4.0 mils/0,102mm
Temperature Class	180°C /356°F
Dielectric Breakdown ¹	9500 Volts
Insulation Resistance ¹ (megohms)	>1 x 10 ⁶
Breaking Strength ¹	20 lbs./in. (35 n/10mm)
Elongation ¹ (% at break)	200
Electrolytic Corrosion Factor ²	1.0
Adhesion to Steel ¹	30 oz./in. (3.2 n/10mm)
Printable	Yes
UL Flame Retardant ³	Yes

* Footnote: 1. Test method ASTM D 1000
2. 3M Test Method-Available on request
3. UL-recognized for flame retardancy per UL 510, Product Category 0ANZ2, File E17385.

3M is a trademark of 3M.

Important Notice

All statements, technical information and recommendations related to the Seller's products are based on information believed to be reliable, but the accuracy or completeness thereof is not guaranteed. Before utilizing the product, the user should determine the suitability of the product for its intended use. The user assumes all risks and liability whatsoever in connection with such use.

Any statements or recommendations of the Seller which are not contained in the Seller's current publications shall have no force or effect unless contained in an agreement signed by an authorized officer of the Seller.

The statements contained herein are made in lieu of all warranties, expressed or implied, including but not limited to the implied warranties of merchantability and fitness for a particular purpose which warranties are hereby expressly disclaimed.

SELLER SHALL NOT BE LIABLE TO THE USER OR ANY OTHER PERSON UNDER ANY LEGAL THEORY, INCLUDING BUT NOT LIMITED TO NEGLIGENCE OR STRICT LIABILITY, FOR ANY INJURY OR FOR ANY DIRECT, INDIRECT, SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES SUSTAINED OR INCURRED BY REASON OF THE USE OF ANY OF THE SELLER'S PRODUCTS THAT WERE DEFECTIVE.



Electrical Products Division

6801 River Place Blvd.
Austin, TX 78726-9000
800 676 8381
<http://www.3m.com/elpd>

© 3M 1998
78-8124-4716-3