

# Bond just about anything with one versatile tape!

## Applications:

- POP/POS Displays
- Light Boxes
- Indoor/Outdoor Signs
- Paper Bonding and Packaging
- Metal Fabrication
- Splicing and Bonding
- Sports Equipment
- Home Decoration
- Mounting of Plastic Parts
- Mounting in Electronics
- Mounting in Furniture



### 3M™ High Performance Double Coated Tape 9088-200 and 9088F200

	9088-200	9088F200
<b>Total Tape Thickness Without Liner</b> mils/μm	7.9/200	7.9/200
<b>Color</b>	Clear	Clear
<b>Carrier Type</b>	PET	PET
<b>Thickness, mils/μm</b>	3.7/9.4	3.7/9.4
<b>Liner Type</b>	58# Glassine	Red Polypropylene Film
<b>Thickness, mils/μm</b>	3.2/8	3.2/8
<b>Substrate Compatibility</b>	ABS, PET, PVC, Foil, Glass, Metal, Paper, Plastic, Polystyrene, Polypropylene, Polycarbonate, Powder Coated Paint	
<b>Adhesive</b>	Solventless Modified Acrylic	Solventless Modified Acrylic
<b>Temperature Range</b> Short Term / Long Term	148°C (300°F) / 90°C (194°F)	148°C (300°F) / 90°C (194°F)

## Markets:

- Transportation
- Appliance
- Automotive
- Construction
- Signage
- Electronics
- General Industrial

**Warranty, Limited Remedy, and Disclaimer:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



**Converter Markets**  
**Industrial Adhesives and Tapes Division**  
 3M Center, Building 225-3S-06  
 St. Paul MN 55144-1000  
 1-800-328-1681  
[www.3M.com/converter](http://www.3M.com/converter)


3M, Scotch and the Plaid Design  
 are trademarks of 3M Company.

Please recycle. Printed in U.S.A.  
 © 3M 2016. All rights reserved.  
 70-0713-4623-6

**3M** Science.  
Applied to Life.™

3M™ High Performance Double Coated Tape  
9088-200 and 9088F200

# The Power of Possibilities



Versatility With  
a Purpose...  
Strength and  
Sustainability

The New Standard in General Purpose Industrial Tape

## 3M™ High Performance Double Coated Tape 9088-200 and 9088F200



9088-200  
Paper liner



9088F200  
Film liner

Value-priced, durable, general purpose tapes have a wide service temperature range from -10°F (-23°C) to 300°F (148°C) as well as:

- High peel and shear strength
- High initial tack
- Excellent UV resistance
- Chemical resistance – including plasticizers used in many plastic materials
- Excellent transparency – leaves no visible bond lines, making it great for laminating
- Adhesive lays down flat for a smoother surface
- Ideal for many low and high surface energy bonding applications
- Uses a solventless adhesive coating process that is good for the environment and application performance

**Bond just about anything –  
with one, versatile RED tape!**

Available with paper or film liner

## With both the paper and film liner, you can take on almost any project

- Bond most any substrate with a single product – from glass, metal and powder coated paint to most common plastics
- Works on both LSE and HSE surfaces
- Easy to cut, resistant to tearing and available in a variety of sizes
- Replace mechanical fasteners – like screws, bolts and rivets in many applications
- Solvent-free formula
- Low odor
- Available in level wound rolls



▶ 3M™ High Performance Double Coated Tape 9088F200 with a film liner has the same attributes of the paper liner as well as:

- No debris – “clean”
- Crisp die-cutting – especially rotary
- Fast processing with small pieces
- Useful for laser registration – color dependent
- Improved visibility and transparency

