

DYMO®



LabelWriter™ 450

PROFESSIONAL LABEL PRINTER FOR PC AND MAC®


- Save time - print up to 51 labels per minute*
- No expensive ink or toner needed - uses thermal printing technology
- Create custom labels from 60+ label styles and layouts
- Prints crystal-clear barcodes, labels and graphics with 600 x 300 dpi resolution
- Eliminate the waste and hassles - print precise quantities and create labels directly from Microsoft® Word, Excel® Outlook®, Google Contacts® with DYMO® Connect for Desktop Software
- For even more features, download DYMO® Connect for Desktop Software

* 4-line address label



Single Unit Includes:

- LabelWriter 450
- Address Labels Starter Roll
- Power Adapter
- Power Cable
- USB Cable
- Quick Start Guide
- 2 + 1 - Year Limited Warranty**



Quick Specs

Unit Dimensions (H x W x L)	134 x 187 x 127 mm
Weight	1.3 kg
Mac®/PC Compatible	Yes via DYMO® Connect for Desktop Software
Max Label Width	58.42 mm
Resolution	600 x 300 dpi
Printing System	Direct Thermal
Print Speed	51 labels/minute*
Barcodes	Yes
Power Source	Adapter Power Cable
Networking	Print Server Sold Separately
Country of Origin	China

Item Number	Description	Unit	Length (cm)	Width (cm)	Height (cm)	QTY	EAN	Customer Price
S0838770	LabelWriter 450	Unit	14.0	27.0	16.3	1	3501170838778	

** +1 year if registered on the DYMO® website

LW Standard labels

Hassle-free labels for all your mailing, shipping and organizational needs.

Label Type	Description	Code #	Size (mm)	Rolls/Box	Labels/Roll	Adhesive	Material
Mailing	Standard Address Labels	S0722370	28 x 89	2	130	Permanent	Paper
	Standard Address Labels	S0722360	28 x 89	24	130	Permanent	Paper
	Standard Address Labels	2093091	28 x 89	12	130	Permanent	Paper
	Assorted Colour Labels	S0722380	28 x 89	4	130	Permanent	Paper
	Large Address Labels	S0722400	36 x 89	2	260	Permanent	Paper
	Large Address Labels	S0722390	36 x 89	24	260	Permanent	Paper
	Large Address Labels	2093093	36 x 89	12	240	Permanent	Paper
	Large Address Labels	S0722410	36 x 89	1	260	Permanent	Transparent Plastic
	Large Return Address Labels	S0722520	25 x 54	1	500	Permanent	Paper
Shipping	Shipping / Name Badge Labels	S0722430	54 x 101	1	220	Permanent	Paper
	High Capacity Shipping Labels	S0947420	102 x 59	2	575	Permanent	Paper
	Shipping / Name Badge Labels	2093092	54 x 101	6	220	Permanent	Paper
	Shipping / Name Badge Labels	S0722420	54 x 101	12	220	Permanent	Paper
	Extra Large Shipping Labels	S0904980	104 x 159	1	220	Permanent	Paper
Multi-Purpose	Multi-Purpose Labels	S0722530	13 x 25	1	1000	Removable	Paper
	Square Multi-Purpose Labels	S0929120	25 x 25	1	750	Removable	Paper
	Multi-Purpose Labels	S0722550	19 x 51	1	500	Removable	Paper
	Multi-Purpose Labels	S0722540	32 x 57	1	1000	Removable	Paper
	Large Multi-Purpose Labels	S0722440	54 x 70	1	320	Permanent	Paper
	Large Multi-Purpose Labels	2093094	32 x 57	6	1000	Permanent	Paper
	Large Multi-Purpose Labels	2093095	32 x 57	12	1000	Permanent	Paper
Specialty	Suspension File Labels	S0722460	12 x 50	1	220	Permanent	Paper
	Small Lever Arch File Labels	S0722470	38 x 190	1	110	Permanent	Paper
	Large Lever Arch File Labels	S0722480	59 x 190	1	110	Permanent	Paper
	Small Name Badge Labels	S0722560	41 x 89	1	300	Removable	Paper
	Appointment / Name Badge Cards	S0929100	51 x 89	1	300	Non-adhesive	Paper

LW Durable Labels

Tear-resistant, coated polypropylene labels with extra-strength adhesive that withstand abrasion, common cleaners, and a wide range of temperatures-ideal for shelving, storage, and signage.



Water



Solvents



Oil



Textured Surfaces



Temperature
-18°C to 50°C

Label Type	Description	Code #	Size (mm)	Rolls/Box	Labels/Roll	Adhesive	Material
Durable	LW Durable Labels	1933081	25 x 89	1	350	Permanent	Coated Polypropylene
	LW Durable Labels	1933083	25 x 25	2	850	Permanent	Coated Polypropylene
	LW Durable Labels	1933084	32 x 57	1	800	Permanent	Coated Polypropylene
	LW Durable Labels	1933085	19 x 64	2	450	Permanent	Coated Polypropylene
	LW Durable Labels (4XL only)	1933086	104 x 159	1	200	Permanent	Coated Polypropylene
	LW Durable Labels	1933087	59 x 190	1	170	Permanent	Coated Polypropylene
	LW Durable Labels	1933088	59 x 102	1	300	Permanent	Coated Polypropylene
	LW Durable Labels	1976411	25 x 54	1	160	Permanent	Coated Polypropylene

The DYMO® high quality labels are made in Belgium