RF Cable Assembly MMCX R/A Plug - Straight Plug



RoHS Compliant



Specifications

Cable Length : 95mm / 3.74"

Connector Type A : MMCX Right Angle Plug Connector Type B : MMCX Straight Plug

Voltage Rating : 250V RMS Insulation Resistance : $1,000M\Omega$ Min.

Dielectric Withstanding Voltage : 500V AC / 1 min. hold with no breakdown or flashover

MMCX Contact Resistance : Centre Contact: $5m\Omega$ Max. Outer Contact: $2.5m\Omega$ Max.

Mating : Snap-on Coupling


Durability : 500 times

Body Material : Brass/Beryllium Copper, Gold Plated

Centre Contact Material : Brass, Gold Plated

Insulating Material : PTFE

Diagram



Part Number Table

Description	Part Number
RF Cable Assembly, MMCX R/A Plug – Straight Plug with RG-174, 95mm	MC002991

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

