

Han-Modular Flexbox hood 3 entries



Part number	09 14 000 8013
Specification	Han-Modular Flexbox hood 3 entries
HARTING eCatalogue	https://b2b.harting.com/09140008013

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Modular [®] Flexbox
Type of hood/housing	Hood
Version	
Version	Top entry
Cable entry	3x
Technical characteristics	
Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP54
Clamping range	5 24 mm
Material properties	
Material (hood/housing)	Polyamide (PA) Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e

Page 1 / 2 | Creation date 2020-03-18 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties

REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61984 EN 45545-1 R22: HL1, HL2
Commercial data	
Packaging size	1
Net weight	109.6 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors