

(includes 303 4458-5311 1000
303 4483-5311 1060)



Produktcertificate		
SKINTOP® ST-M / STR-M		gültig ab : 08.03.99

The polyamide based SKINTOP ST-M / STR-M is designed for universal use, above all for functional safety in manufacturing of machines and equipment, in measuring, controlling and automation, as well as in the electronic technology and in manufacturing of robots.

The gland make-up consists of:

- | | |
|------------------------------------|------------------------------------|
| ◆ gland body with lamellar design | polyamide based plastic (UL 94-V2) |
| ◆ cap nut | polyamide based plastic (UL 94-V2) |
| ◆ seal insert | elastomere |
| ◆ sealing ring (M 40x1,5-M 63x1,5) | elastomere |

Technical features:

connecting thread:	M 12x1,5-M 63x1,5 in acc. to DIN 13 Teil 6
functional thread:	multi-start trapezoidal thread at M 12x1,5-M 32x1,5 single-start trapezoidal thread at M 40x1,5-M 63x1,5
IP protection:	IP 68 - 5 bar/30 min., test in acc. to DIN 40 050, with o-ring at the connecting thread (M40 - M63)
strain relief:	at the moment like DIN VDE 0619
temperature range:	- 20° C up to + 80° C
type:	ST-M = standard ; STR-M = standard with reducing seal insert
* approval :	cURus / cULus file Nr. E 79903 *

For more information please see our current catalogue.
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

With kind regards

Oskar Lapp Limited
46-50 Standard Road
London NW10 6EF
Tel 0208 961 5855
Fax: 0208-965-2780

Development Department

Sales
[Handwritten Signature]