

**SOLDIP SOLDER POT SPECIFICATIONS**

Specification	Major	Minor
Input power (volts)	115 or 230	115 or 230
Wattage	60w	45W
Stabilised run temp.	280° C nominal	280° C nominal
Full solder capacity	17 cm <sup>3</sup>	9.5 cm <sup>3</sup>
Normal solder depth	17 cm	14 cm
Max depth at centre	57	14
Mains lead length	1.5 m	1.5 m
Tilt with stability	45°	45°
Weight (empty)	960 gms	770 gms
Heating elements	2 (3 for 115v)	2
Electrical leakage at 1250 a.c.	0.15 mA	0.15 mA