



ABI Electronics Ltd
 Dodworth Business Park
 Dodworth
 BARNESLEY
 South Yorkshire S75 3SP
 United Kingdom
 tel: (+44) 1226 207420
 fax: (+44) 1226 207620
 web: www.abielelectronics.co.uk

LinearMaster Compact device list

ANALOG IC TESTER, SOFTWARE VERSION LMC/1.31

<u>OPERATIONAL AMPLIFIERS</u>		LM218 (1)	218	RC4558	4558
AD546	546	LM224	224	TL061	061
AD548	548	LM248	248	TL062	062
AD645	645	LM258	258	TL064	064
AD648	648	LM301	301	TL071	071
AD711	711	LM307	307	TL072	072
AD712	712	LM308	308	TL074	074
AD713	713	LM318 (1)	318	TL081	081
AMP03	03	LM324	324	TL082	082
CA1458	1458	LM348	348	TL084	084
CA3080	3080	LM358	358	TLC271	271
CA3130	3130	LM2900	2900	TLC272	272
CA3140	3140	LM2902	2902	TLC274	274
CA3160	3160	LM2904	2904	TLC277	277
CA3240	3240	LM3900	3900	TLC279	279
CA3260	3260	LMC660	660	TLC1079	1079
CA5130	5130	LMC6032	6032	TLC2272	2272
CA5160	5160	LMC6042	6042	TLC2872	2872
CA5260	5260	LP124	124	TLE2061	2061
HA3-2840-5	328405	LP324	324	TLE2062	2062
ICL7611	7611	LT1013	1013	TLE2064	2064
ICL7612	7612	LT1014	1014	TLE2071	2071
ICL7621	7621	MAX407	407	TLE2072	2072
ICL7641	7641	MAX427	427	TLE2074	2074
ICL7642	7642	MC3303	3303	TLE2081	2081
LF147	147	MC3403	3403	TLE2082	2082
LF155	155	MC33171	33171	TLE2084	2084
LF255	255	MC33172	33172	TLE2161	2161
LF347	347	MC33174	33174	uA709	709 (8 pin)
LF351	351	NE531	531	uA709	709 (14 pin)
LF353	353	NE5532	5532	uA741	741
LF355	355	NE5534	5534	uA747	747
LF411	411	OP07	07	uA748	748
LF412	412	OP27	27		
LM11	11	OP37	37		
LM101	101	OP42	42		
LM107	107	OP77	77		
LM108	108	OP90	90		
LM118 (1)	118	OP97	97		
LM124	124	OP200	200		
LM148	148	OP290	290		
LM158	158	OP482	482		
LM201	201	OP490	490		
LM207	207	OPA121	121		
LM208	208	OPA606	606		

COMPARATORS

CMP04	04
LM111	111
LM119	119
LM139	139
LM193	193
LM211	211
LM219	219
LM239	239
LM293	293
LM311	311
LM319	319
LM339	339
LM393	393
LM2901	2901
LM2903	2903
LM3302	3302
LP111	111
LP211	211
LP311	311
LP239	239
LP265	265
LP339	339
LP365	365
LP2901	2901
LT1016	1016
TLC339	339
TLC372	372
TLC393	393
TLC3702	3702
TLC3704	3704

**OPERATIONAL
AMPLIFIERS/
COMPARATORS**

LM392	392
LM2924	2924

VOLTAGE REGULATORS

uA7805 (2)	7805
uA7905 (2,3)	7905
LM2930-5 (3)	29305
LM2931-5 (3)	29315
LM340T5 (2)	3405
MAX667	667

VOLTAGE REFERENCES

REF02	02
REF03	03
REF05	05
REF43	43
MAX872	872

**ANALOG SWITCHES
/MULTIPLEXERS**

4016	4016
4051	4051
4052	4052
4066	4066
4529	4529
DG201	201
DG211	211
DG212	212
DG308	308
DG309	309
DG411	411
DG412	412
DG413	413
DG417	417
DG418	418
DG419	419
DG508	508
LF13201	13201
LF13202	13202
LF13508	13508

TRANSISTOR ARRAYS

ULN2001	2001
ULN2003	2003
ULN2004	2004
ULN2005	2005
ULN2064	2064
ULN2065	2065
ULN2068	2068
ULN2069	2069
ULN2074	2074
ULN2075	2075

**OPTOISOLATORS/
OPTOCOUPERS**

4N25	425
4N26	426
4N27	427
4N28	428
4N29	429
4N30	430
4N31	431
4N32	432
4N33	433
4N35	435
4N36	436
4N37	437
6N135	6135
6N136	6136
HCPL2530	2530
HCPL2531	2531
HCPL4502	4502
HCPL4503	4503
ILD74	74
ISD74	74
ILCT6	6

LD428	428
MCT2	2
MOC8030	8030
TIL197	197
TIL198	198
TIL199	199
TLP250250	
TLP559559	
TLP621621	

DACS/ADCS

AD7524	7524
DAC08	08
DAC0800	0800
TLC7524	7524

SPECIAL FUNCTIONS

NE555 (4)	555
NE556	556
TLC555	555
TLC556	556

VIRTUAL GROUNDS

TLE2425 (2)	2425
TLE2426 (2)	2426

AUDIO

L272	272
------	-----