DATA SHEET

CAT6APC SERIES, UNSHIELDED

CAT6A NETWORK COPPER PATCH CABLE, UTP

24/7 TECHNICAL SUPPORT AT 877.877.2269 OR VISIT BLACKBOX.COM





OVERVIEW

CAT6A 500 MHZ STRANDED PATCH CABLE –UNSHIELDED (UTP), PVC, SNAGLESS BOOTS (CAT6APC SERIES)

INTRODUCTION

Black Box® GigaTrue® Premium CAT6A Patch Cables exceed TIA/EIA 568.2-D CAT6A industry standards. Offering superior near-end crosstalk (NEXT) compared to standard CAT6A cable, these cables ensure transmission of your voice, data, AV, and/or PoE signals in bandwidth-intensive 10G networking applications. They feature a robust four-pair 24-AWG construction and 50-micron gold-plated contacts for superior conductivity. These cables also have connectors designed for an insertion and extraction life of 750 cycles, making for an ultra-reliable solution that you can count on to perform.

FEATURES

- PREMIUM CABLE CONSTRUCTED TO EXCEED INDUSTRY STANDARDS.
- 50-MICRON GOLD-PLATED CONTACTS PROVIDE SUPERIOR CONDUCTIVITY.
- CABLING ETL VERIFIED TO ANSI/TIA 568.2-D.
- CONNECTOR DESIGNED FOR AN INSERTION AND EXTRACTION LIFE OF 750 CYCLES.
- THIS CABLE OFFERS SUPERIOR NEAR-END CROSSTALK (NEXT) COMPARED TO STANDARD CAT6A CABLE.
- SNAGLESS BOOTS PREVENT CONNECTOR DAMAGE DUE TO SNAGS DURING INSTALLATION.
- FLUSH FIT STRAIN RELIEF BOOT PERFECT FOR HIGH-DENSITY APPLICATIONS.

SPECIFICATIONS

SPECIFICATIONS FOR CAT6A CABLE										
MODEL	COLOR	AWG	WIRE	SHIELD	JACKET	SNAGLESS	MOLDED PLUG	MHZ	LENGTH	50µ PLATING
CAT6APC-003-BK	Black	24	Stranded	No	СМ	Yes	Yes	500	3 ft. (0.91 m)	Yes
CAT6APC-003-BL	Blue	24	Stranded	No	СМ	Yes	Yes	500	3 ft. (0.91 m)	Yes
CAT6APC-005-BK	Black	24	Stranded	No	СМ	Yes	Yes	500	5 ft. (1.52 m)	Yes
CAT6APC-005-BL	Blue	24	Stranded	No	СМ	Yes	Yes	500	5 ft. (1.52 m)	Yes
CAT6APC-007-BK	Black	24	Stranded	No	СМ	Yes	Yes	500	7 ft. (2.13 m)	Yes
CAT6APC-007-BL	Blue	24	Stranded	No	СМ	Yes	Yes	500	7 ft. (2.13 m)	Yes
CAT6APC-010-BK	Black	24	Stranded	No	СМ	Yes	Yes	500	10 ft. (3.05 m)	Yes
CAT6APC-010-BL	Blue	24	Stranded	No	СМ	Yes	Yes	500	10 ft. (3.05 m)	Yes
CAT6APC-014-BK	Black	24	Stranded	No	СМ	Yes	Yes	500	14 ft. (4.27 m)	Yes
CAT6APC-014-BL	Blue	24	Stranded	No	СМ	Yes	Yes	500	14 ft. (4.27 m)	Yes
CAT6APC-020-BK	Black	24	Stranded	No	СМ	Yes	Yes	500	20 ft. (6.10 m)	Yes
CAT6APC-020-BL	Blue	24	Stranded	No	СМ	Yes	Yes	500	20 ft. (6.10 m)	Yes
CAT6APC-025-BK	Black	24	Stranded	No	СМ	Yes	Yes	500	25 ft. (7.62 m)	Yes
CAT6APC-025-BL	Blue	24	Stranded	No	СМ	Yes	Yes	500	25 ft. (7.62 m)	Yes



2

ORDERING INFORMATION

CAT6A 500-MHZ STRANDED ETHERNET PATCH CABLE – UNSHIELDED (UTP), PVC, SNAGLESS BOOTS (CAT6APC SERIES)

LENGTH	COLOR	MODEL
3-ft.	Black	CAT6APC-003-BK
3-ft.	Blue	CAT6APC-003-BL
5-ft.	Black	CAT6APC-005-BK
5-ft.	Blue	CAT6APC-005-BL
7-ft.	Black	CAT6APC-007-BK
7-ft.	Blue	CAT6APC-007-BL
10-ft.	Black	CAT6APC-010-BK
10-ft.	Blue	CAT6APC-010-BL
14-ft.	Black	CAT6APC-014-BK
14-ft.	Blue	CAT6APC-014-BL
20-ft.	Black	CAT6APC-020-BK
20-ft.	Blue	CAT6APC-020-BL
25-ft.	Black	CAT6APC-025-BK
25-ft.	Blue	CAT6APC-025-BL

ACCESSORIES	
NAME	MODEL
CAT6A Keystone Jack - Unshielded, RJ-45, Blue	C6AJA70-BL-R2
CAT6A Keystone Jack - Unshielded, RJ-45, Blue, 25-Pack	C6AJA70-BL-R2- 25PAK
CAT6A Staggered Feed-Through Patch Panel - 2U, Shielded, 48-Port	C6AFP70S-48
CAT6A Staggered Multimedia Patch Panel - 1U, Blank, 24-Port	C6AMP70-24
CAT6A Staggered Multimedia Patch Panel - 2U, Blank, 48-Port	C6AMP70-48
CAT6A Component Level 110 Patch Panel - 1U, Rackmount, PoE+, 24-Port	C6APP70-24

DISCLAIMER

Black Box Corporation shall not be liable for damages of any kind, including, but not limited to, punitive, consequential or cost of cover damages, resulting from any errors in the product information or specifications set forth in this document and Black Box Corporation may revise this document at any time without notice.

TRADEMARKS

Black Box and the Black Box logo type and mark are registered trademarks of Black Box Corporation.

Any other trademarks mentioned in this document are acknowledged to be the property of the trademark owners.

FILENAME: CAT6APC-003-XXX_DS_REV1.PDF © COPYRIGHT 2020. BLACK BOX CORPORATION. ALL RIGHTS RESERVED.

