

Datasheet

Industrial Style Duplex Thermocouple with KNE Terminal Head – Type K



Industrial Style Duplex Thermocouple with Terminal Head available in type K

- Weatherproof aluminium IP67 terminal head with screw fit lid
- 6mm Diameter sheath
- 150, 250 & 500 mm lengths available
- Type K Duplex Sensor range: -100 to 1100°C
- Fitted with duplex type K terminal block

KNE Terminal head

Head Type	KNE Standard Head
Material	Aluminium silver painted
Cable Entry	M20 x 1.5mm
Fixing (Centres)	33mm & 40mm
Max. Temperature	170°C
IP Rating	IP67 rated
Cap Retaining Type	Screw cap and retaining screw

Probe Length

Order Code

150mm	XF-1444-FAR
250mm	XF-1445-FAR
500mm	XF-1446-FAR