

由 Autodesk 教育版产品制作

1. 100% OPEN SHORT MIS WIRE TEST 2. CONTACT RESISTANCE:5 OHM MAX 3. INSULATION RESISTANCE:5M OHM MIN 4. HI-POT TEST:DC 300V/10ms 5. PASS 1920*1080P/60HZ EST	CONSUMER ITEM	LENGTH (mm)
	PSG3316	200±10

USB 3.1 C/M Nickel plated

6.65±0.15

P1



white PVC Model


Cable:

USB3.1 (#32*1P+D+AL+MY)*4C+#32*4C+#32*1P+#26*1C+#28*1C+AB white PVC Jacket OD4.0MM


silvery Metal shell

VGA/F
Nickel plated




P2



B11 B10B8A5 B5B3B2 VBUS




A11A10A8A7A6A3A2GND



RTD2169 E1103030

silvery Metal shell



				DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	1RD ANGLE
				MODEL NO.		△			
APPROVED	CHECKED	DRAWING	DESIGNED	DRAWING NO.	256-045	△			
				FINISHING		△	2020/6/23		A1
				MATERIAL		SYM	DATE		REVISION

QR-025 2007.05.03, A1