

# MEACO 12L-AH Dehumidifier

'Works best in flats through to three bedroom houses to remove excess moisture from the air and prevent condensation, mould and damp issues'



U Galicico



12

## **MEACO 12L-AH DEHUMIDIFIER**

The Meaco 12L-AH is a new 12 litre compressor dehumidifier for 2016 offering a stylish choice for those who need a dehumidifier but appreciate good design.

It stands out from other dehumidifiers thanks to its cuboid like design with a double sided air intake topped off with a circular, control panel complete with large, colour changing digits.

Externally the look of the Meaco 12L-AH might be different but internally it has the same quality components upon which we have built our reputation for solid, reliable dehumidifiers. It will deal with mould, condensation and damp in apartments through to 3 bedroom houses.

#### **CHEAP TO RUN**

Power consumption is rated at just 183 watts at 20°C and 60%rh which would be typical of conditions in a British home. At these conditions the Meaco 12L-AH, based on an electricity charge of 15.32pence/kWh, would cost you just 2.78pence/hour to run.

It has a large digital display with colour changing digits (depending on how damp the air is) to show you the current room readings and to set your target relative humidity, a 1 - 24 hour off timer and a double sided air inlet with combined dust and charcoal filter.

When the relative humidity in your home is below the mould growth level the display on the Meaco 12L-AH will display the readings in blue, outside of this comfort zone it will display the readings in red or green to warn you if your home is becoming too damp or too dry.

The dual air inlet has a double walled filter removing both dust particles and smells from the air thanks to its combined particle and charcoal filter.



### LARGE COLOUR CHANGING DISPLAY



Meaco (U.K.) Limited, Meaco House, Parklands, Railton Road, Guildford, Surrey, GU2 9JX t: 01483 234900 e: sales@meaco.com **www.meaco.com** 

## **SPECIFICATIONS**

Drying Capacity (Litres/24 Hours)	26.7°C - 60%rh	6 litres
	30.0°C - 80%rh	12 litres
Power Consumption (Watts)	20.0°C - 60%rh	183 watts
	26.7°C - 60%rh	190 watts
	30.0°C - 80%rh	235 watts
Air Flow (m³/hr)		120
Auto restart		Yes
Noise (dB)		≤45
Tank Size		1.7 litres
Timer		1-24 hour off timer
Castors		Yes
Temperature Range		+5°C/+38°C
Relative Humidity Range		30% - 95%rh
Refrigerant		R134a/100g
Rated Voltage		220-240V/50Hz
Dehumidifier Dimensions (mm - w x d x h)		255 x 245 x 495
Box Dimensions (mm - w x d x h)		306 x 288 x 528
Nett/Gross Weight (Kgs)		10.5/11Kgs

## **APPLICATIONS**





Condensation









Bathroom



Flats to 3 bedroom houses

Laundry drying



Kitchen



Low running costs