
BULGIN Battery Holders

Panel Mounting




- Battery size D (R20)
- 1, 2 or 3 Cells
- Flanged Panel Mount
- Bayonet/Screwdriver release






- Battery size PP3 (6R61)
- 1 Cell
- Flanged Panel Mount
- Drawer function





10

- Battery size PP3 (6R61)
- 2 Cells
- Flanged Panel Mount
- Drawer function



Specification	BX0016, BX0017, BX0018	BX0023	BX0026
Battery/Cell Type:	D (R20)	PP3 (6R61)	PP3 (6R61)
No. Cells:	BX0016 -1 cell BX0017 - 2 cells BX0018 - 3 cells	1 cell	2 cells
Terminations:	4.8 series tabs/solder tags	Solder tag	Solder tag
Operating Temperature:	-30°C to +70°C	-30°C to +70°C	-30°C to +70°C
Mouldings:	Nylon & Polycarbonate	Glass Filled Nylon	Glass Filled Nylon
Contacts:	Brass, Nickel Plated	Phosphor Bronze, Tin Plated	Phosphor Bronze, Tin Plated
Features:	Bayonet cap with coin slot. Body may be supported by rear bracket	Removable loading drawer	Removable loading drawers