

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

Part Number: 2157112125

**Status:** **Active**

**Overview:** Off-the-Shelf Pre-Crimped Leads

**Description:** Pre-Crimped Lead Clic-Mate Male-to-Pigtail, Tin (Sn) Plated, 450.00mm Length, 24 AWG. Red

## Documents:

Drawing (PDF)

[RoHS Certificate of Compliance \(PDF\)](#)

## General

|                        |                                        |
|------------------------|----------------------------------------|
| Product Family         | Cable Assemblies                       |
| Series                 | <u>215711</u>                          |
| Application            | Signal, Wire-to-Board                  |
| Assembly Configuration | Pre-crimped Lead Only                  |
| Connector to Connector | CLIK-Mate-to-CLIK-Mate                 |
| Overview               | <u>Off-the-Shelf Pre-Crimped Leads</u> |
| Product Name           | CLIK-Mate                              |
| UPC                    | 193264605354                           |

## Physical

|                                |                      |
|--------------------------------|----------------------|
| Cable Length                   | 450.00mm             |
| Circuits (Loaded)              | 1                    |
| Color - Resin                  | Red                  |
| Gender                         | Male-Pigtail         |
| Material - Metal               | Copper Alloy         |
| Material - Plating Mating      | Tin                  |
| Material - Plating Termination | Tin                  |
| Net Weight                     | 1.520/g              |
| Packaging Type                 | Bag                  |
| Plating min - Mating           | 0.406μm              |
| Plating min - Termination      | 0.406μm              |
| Single Ended                   | Yes                  |
| Termination Interface: Style   | Crimp or Compression |
| Wire Insulation Diameter       | 0.78-1.28mm          |
| Wire Size AWG                  | 24                   |
| Wire/Cable Type                | UL 10002             |

## Electrical

|                               |                  |
|-------------------------------|------------------|
| Current - Maximum per Contact | 2.0A             |
| Voltage - Maximum             | 100V AC (RMS)/DC |

## Material Info

### Reference - Drawing Numbers

|               |                |
|---------------|----------------|
| Sales Drawing | 2157111121-000 |
|---------------|----------------|



Series image - Reference only

## EU ELV

**Not Relevant**

## EU RoHS

## Compliant

## REACH SVHC

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

### Halogen-Free

## Status

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

## RoHS Phthalates

## China RoHS

Green Image

Not Relevant

Not Contained

### Search Parts in this Series

215711 Series

## Use With

CLIK-Mate Housing 502578 , 503149

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**