

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2147512032](#)  
**Status:** **Active**  
**Overview:** Micro-Fit Connector System  
**Description:** Micro-Fit 3.0 Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, Gold (Au) Plating, 3 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">214751</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Fit 3.0-to-Pigtail
Overview	<u>Micro-Fit Connector System</u>
Product Name	Micro-Fit 3.0
Type	Discrete Wire Assembly
UPC	193264585519

**Physical**

Cable Length	300.00mm
Circuits (Loaded)	3
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	10.990/g
Number of Rows	1
Pitch - Mating Interface	3.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Single Ended	Yes
Wire Insulation Diameter	1.85mm max.
Wire Size AWG	18
Wire/Cable Type	Discrete Wire, UL 10002


**Electrical**

Current - Maximum per Contact	8.5A
-------------------------------	------

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	2147512031-000
---------------	----------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[214751](#) Series

**Mates With**

Micro-Fit 3.0 Plug Housings [43640](#)

<br>Micro-Fit TPA Plug Housing [200875](#)

<br>Micro-Fit 3.0 Headers [43650](#)