

16



NES/J 210

Power supply connectors



Power supply plug, long, straight version, with solder eyes

State: Active



Environmental conditions

Temperature range -20 °C/+70 °C

Materials

Insulating body	PC
Contact	CuZn, nickel-plated
Insulation	ABS/PVC
Housing	ABS

Mechanical data

Outer diameter	5,5 mm
Inner diameter	2,1 mm













Connectable conductors for solder area

Cable diameter 4 mm

Electrical data (at T_{amb} 20 °C)

Rated current	0,5 A
Rated voltage	12 V DC
Rated impulse voltage	500 V/60 s
Insulation resistance	≥ 100 M Ω

Associated products

Counterparts		
 1610 02	 1613 14	 1613 18
 1614 09	 1614 14	 1614 16
 1614 19	 NEB 21 R	 NEB/J 21
 NEB/J 21 C	 NEB/J 21 R	 NEK/J 210

16

NES/J 210

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
NES/J 210	2	100	500

Packaging:

in bulk, in a cardboard box or a plastic bag