

N4234 Chameleon Magnifier Lamp

This white magnifying lamp has 1.75X magnification (3 diopter) in a 7" glass lens.

This lamp has 3 different colour temperatures ranging from 2700K, 4000K, 5500K and each brightness levels, ensuring the user always has the optimal level of light for working on any

The lens can be protected by a cover which is supplied and designed to guard the lens against placed over the lens when the lamp is not in use.

The stable flexible arm on the lamp is covered, making it ideal for cleaning and ensures the long reach of 120cm (47 inches).

This magnifying lamp comes with a clamp, which enables it to be locked to desks, benches. The Chameleon Magnifying Lamp is ideal for users who are in industries such as electronic and embroidery.

CE certified – meaning this product can be used within the EU and is supplied with a UK plug.

SKU: N4234



Description

Features

- Three colour temperatures emitted from the LED bulb, range from 2700K, 4000K, 5500K.
- Three brightness levels available for each colour temperature.
- High quality glass lens with 1.75X magnifier.
- Flexible arm to ensure the user can work freely around the lamp.

Technical Details

- Light source: LED
- Lux output at 15cm (6"): 5,000 Lux
- Light colour temperature: 2,700 – 5,500K

- Energy consumption: 28W
- Lens Size: 17cm (7")
- Magnification: 3D (1.75X)
- Lamp diameter: 25cm (10 inches)
- Reach: 120cm (47 inches)
- Clamp depth: 7.3cm (3 inches)
- Weight: 2.57kg
- Colour: White
- Comes with two-year warranty



[Home](#) | [Our Products](#) | [Blog](#) | [Stockists](#) | [Terms & Conditions](#) | [Sitemap](#)

Copyright © 2020 Native Lighting | Trading as Native Lighting Limited, Company Number 12162319