



Classic filament LED candles and lusters

Classic LEDCandle ND 2-25W B35 B22 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

General Information	
Cap-Base	B22 [B22]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	2-25W
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	125.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	2 W

Lamp Current (Nom)	20 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	36 ℃
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Consumption kWh/1000 h	2 kWh


Datasheet, 2020, July 20 data subject to change

Classic filament LED candles and lusters

Product Data	
Full product code	871869676690300
Order product name	Classic LEDCandle ND 2-25W B35 B22 827 CL
EAN/UPC - Product	8718696766903
Order code	929001815602
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001815602
Net Weight (Piece)	0.014 kg


Dimensional drawing




Candle 230V 2-25W 250lm 2700K B22 ND B35

Product D C Classic LEDCandle ND 2-25W B35 B22 827 CL 35 mm 93 mm


Photometric data



CLA LEDcandle 25W B22 827 CL B35




CLA LEDcandle 25W B15 827 CL B35




LEDbulb 40W B22 827 CL A60 ND

Classic filament LED candles and lusters

Lifetime





LEDbulb 60W E14 827 FR B38

LEDbulb 60W E14 827 FR B38



© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.