



# Wi-Fi 6/6E TRIPLE BAND EMBEDDED ANTENNA

Part Numbers: 2344655-1, 2344655-2 2344655-3, 2344655-4 2344655-5, 2344655-6 2344655-7, 2344655-8


### **FEATURES & BENEFITS**

- Wi-Fi 6, also including Wi-Fi 6E new 6GHz band, Bluetooth, ZigBee
- Adhesive backing on PCB simplifies mounting within the device
- Omnidirectional coverage
- No matching components required
- Ground-plane independent design
- Different cable length and connector options available


### **SPECIFICATIONS**

Frequency Range (MHz)	2400-2500	5150-5850	5925-7125
VSWR	< 2.7:1	< 1.8:1	< 1.8:1
Average Efficiency	62%	78%	75%
Peak Gain	1.4dBi	3.7dBi	5.9dBi
Average Gain	-2.5dB	-1.3dB	-0.9dB
Power Handling	10 Watt cw		
Feed Point Impedance	50 ohms unbalanced		
Polarization	Linear		
Size	33 mm x 8.0 mm x 1.0 mm		
Weight	< 1.2 g		
Mounting	Adhesive Tape		
Mating Connectors	MHF-type receptacle (TE PN 2337019-1), MHF4-type receptacle (TE PN: 2334884-1)		
Operating Temperature	-40 to +85°C		
Storage Temperature	-40 to +85°C		
Hazardous Materials	A certificate of conformance is available from the product page on TE website.		

# **RF DATA**




#### Efficiency




Data measured in free space and on plastic device enclosure

# **RADIATION PATTERN**




Data measured in free space and on plastic device enclosure

# **KEEP OUT AREA**





- 1. Antenna designed to be mounted on plastic cover.
- 2. Area in blue indicates Keep Out Area
- 3. Contact TE if keep out zone cannot be guaranteed.



Dimension: mm Diagrams is not into scale

#### 8.0<u>0±0.</u>10 <u>1.00ref</u>. TE PART NUMBER XXXX XXX 2344655-x Rev.xx ADHESIVE -33.00±0.10 XXXXXX PART LIST 2344655-\* 90°REF DIMENSION А В A±4,00 50 1 2 100 1.13 B±0.1 3 150 4 200 5 50 6 100 0.81 7 150 8 200

# DIMENSIONS

2344655-1	50	1.97	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344655-2	100	3.94	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344655-3	150	5.91	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344655-4	200	7.87	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344655-5	50	1.97	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
2344655-6	100	3.94	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
2344655-7	150	5.91	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
2344655-8	200	7.87	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	and the second se
PART	MM	INCH	CONNECTOR TYPE	PART NUMBER	IMAGE
NUMBER	CABLE LENGTH ("A") (ON CABL		(ON CABLE)	MATING COMPONE	NTS

### MATING COMPONENTS

### PACKAGING





DESICCANT:1PCS/BAG

50PCS/BUNCH

TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

For phone numbers in other countries, go to te.com/support-center

#### te.com

TE Connectivity, TE Connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2020 TE Connectivity Ltd. family of companies All Rights Reserved.

07/2020

