



2400-2500 & 5150-5875 MHz DUAL BAND WLAN / BLUETOOTH ANTENNA

Part Numbers: 2344654-1, 2344654-2

2344654-3, 2344654-4

2344654-5, 2344654-6

2344654-7, 2344654-8


FEATURES & BENEFITS

- Adhesive backing on PCB simplifies mounting within the device
- Omnidirectional coverage
- Efficient design reduces power usage
- No matching components required
- Ground-plane independent design
- Wide selection of micro-coaxial cable lengths from 50 to 200mm

SPECIFICATIONS

Frequency Range (MHz)	2400-2500	5150-5850		
VSWR	< 3.0:1	< 3.0:1		
Average Efficiency	60%	70%		
Peak Gain	1.5dBi	5.7dBi		
Average Gain	-1.5dB	-1.7dB		
Power Handling	10 Watt cw			
Feed Point Impedance	50 ohms unbalanced			
Polarization	Linear			
Size	30 mm x 9.5 mm x 1.0 mm			
Weight	< 0.8 g			
Mounting	Adhesive Tape			
Mating Connector	MHF-type receptacle (TE PN 2337019-1), MHF4-type receptacle (TE PN: 2334884-1)			
Operating Temperature	-40 to +85°C			
Storage Temperature	-40 to +85°C			
Hazardous Materials	A certificate of conformance is available from the product page on TE website.			

RF DATA






2500

5875

Frequency[MHz]


Data measured in free space and on plastic board.

RADIATION PATTERN




Data measured in free space and on plastic board.

KEEP OUT AREA



NOTES


- 1. Antenna designed to be mounted on plastic cover.
- 2. Area in blue indicates Keep Out Area
- 3. Contact TE if keep out zone cannot be guaranteed.



Dimension: mm

Diagrams is not into scale


DIMENSIONS




MATING COMPONENTS


2344654-1	50	1.97	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344654-2	100	3.94	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344654-3	150	5.91	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344654-4	200	7.87	MHF-TYPE PLUG	RECEPTACLE (TE PN: 2337019-1)	
2344654-5	50	1.97	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
2344654-6	100	3.94	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
2344654-7	150	5.91	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
2344654-8	200	7.87	MHF4-TYPE PLUG	RECEPTACLE (TE PN: 2334884-1)	
PART	MM	INCH	CONNECTOR TYPE	PART NUMBER	IMAGE
NUMBER	JMBER CABLE LENGTH ("A") (ON CABLE		(ON CABLE)	MATING COMPONE	NTS

PACKAGING





200PCS/BAG DESICCANT:1PCS/BAG



TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752 Canada: +1 (905) 475-6222 Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 UK: +44 (0) 800-267666 France: +33 (0) 1-3420-8686 +31 (0) 73-6246-999 Netherlands: China: +86 (0) 400-820-6015

For phone numbers in other countries, go to te.com/support-center

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2020 TE Connectivity Ltd. family of companies All Rights Reserved.

9-1773982-3 04/20

