

512 SERIES PANEL INDICATOR LED

Part Number	Description
512-501-04	12.7mm MTG FS LENS R 20mA
512-501-20	12.7mm MTG FS LENS R 5/6Vdc
512-501-21	12.7mm MTG FS LENS AlGaAs R 12Vdc
512-501-21-15	12.7mm MTG FS LENS AlGaAs R 12Vdc 15cm FL
512-501-21-50	12.7mm MTG FS LENS R 12VDC
512-501-22	12.7mm MTG FS LENS AlGaAs R 24Vdc
512-501-23	12.7mm MTG FS LENS R 28VDC
512-501-23-19	12.7mm MTG FS LENS R 28VDC 100cm FL
512-501-24	12.7mm MTG FS LENS AlGaAs R 48Vdc
512-501-25	12.7mm MTG FS LENS R 110VDC
512-501-46	12.7mm MTG FS LENS R 35VDC
512-501-72	12.7mm MTG FS LENS AlGaAs R 24VAC
512-501-72-50	12.7mm MTG FS LENS AlGaAs R 24VAC 120mm FL
512-501-72-51	12.7mm MTG FS LENS AlGaAs R 24VAC 120mm FL
512-501-75	12.7mm MTG FS LENS AlGaAs R 110VAC
512-501-75-50	12.7mm MTG FS LENS AlGaAs R
512-501-76	12.7mm MTG FS LENS AlGaAs R 230VAC
512-501-76-50	12.7mm MTG FS LENS AlGaAs R 230VAC Extended Bezel
512-501-86	12.7mm MTG FS LENS R 115VAC
512-521-04	12.7mm MTG FS LENS Y 20mA
512-521-20	12.7mm MTG FS LENS Y 5/6Vdc
512-521-21	12.7mm MTG FS LENS Y 12VDC
512-521-21-15	12.7mm MTG FS LENS Y 12VDC 15cm FL
512-521-21-19	12.7mm MTG FS LENS Y 12VDC 100CM FL
512-521-21-50	12.7mm MTG FS LENS Y 12VDC
512-521-22	12.7mm MTG FS LENS Y 24VDC
512-521-22-19	12.7mm MTG FS LENS Y 24VDC
512-521-23	12.7mm MTG FS LENS Y 28VDC
512-521-25	12.7mm MTG FS LENS Y 110VDC
512-521-46	12.7mm MTG FS LENS Y 35VDC
512-521-75	12.7mm MTG FS LENS Y 110VAC
512-521-76	12.7mm MTG FS LENS Y 230VAC
512-521-76-50	12.7mm MTG FS LENS Y 230VAC 300MM FL
512-532-04	12.7mm MTG FS LENS G 20mA
512-532-20	12.7mm MTG FS LENS G 5/6Vdc
512-532-21	12.7mm MTG FS LENS G 12VDC
512-532-21-15	12.7mm MTG FS LENS G 12VDC
512-532-21-50	12.7mm MTG FS LENS G 12VDC
512-532-21-51	12.7mm MTG FS LENS G 12VDC 2.5M FL
512-532-22	12.7mm MTG FS LENS G 24VDC
512-532-23	12.7mm MTG FS LENS G 28VDC
512-532-23-15	12.7mm MTG FS LENS G 28VDC 15cm FL
512-532-23-19	12.7mm MTG FS LENS G 28VDC
512-532-23-50	12.7mm MTG FS LENS G 28VDC
512-532-23-51	12.7mm MTG FS LENS G 28VDC 2.5M FL
512-532-24	12.7mm MTG FS LENS G 48VDC
512-532-24-50	12.7mm MTG FS LENS G 48VDC 2.5M FL
512-532-25	12.7mm MTG FS LENS G 110VDC
512-532-46	12.7mm MTG FS LENS G 35VDC
512-532-72-51	12.7mm MTG FS LENS AlGaAs G 24VAC 120mm FL
512-532-75	12.7mm MTG FS LENS G 110VAC
512-532-75-15	12.7mm MTG FS LENS G 110VAC
512-532-76	12.7mm MTG FS LENS G 230VAC
512-535-72-50	12.7mm MTG FS LENS Tri Colour R/G/A 24VAC 120mm FL
512-540-21	12.7mm MTG FS LENS R 12VDC Flashing LED
512-930-04	12.7mm MTG FS LENS B 20mA
512-930-20	12.7mm MTG FS LENS B 5/6Vdc
512-930-21	12.7mm MTG FS LENS B 12VDC
512-930-22	12.7mm MTG FS LENS B 24VDC
512-930-23	12.7mm MTG FS LENS B 28VDC
512-930-25	12.7mm MTG FS LENS B 110VDC
512-930-46	12.7mm MTG FS LENS B 35VDC
512-930-75	12.7mm MTG FS LENS B 110VAC
512-930-76	12.7mm MTG FS LENS B 230VAC
512-997-04	12.7mm MTG FS LENS W 20mA
512-997-21	12.7mm MTG FS LENS W 12VDC
512-997-22	12.7mm MTG FS LENS W 24VDC
512-997-23	12.7mm MTG FS LENS W 28VDC
512-997-24	12.7mm MTG FS LENS W 48VDC
512-997-25	12.7mm MTG FS LENS W 110VDC
512-997-46	12.7mm MTG FS LENS W 35VDC
512-997-75	12.7mm MTG FS LENS W 110VAC
512-997-75-50	12.7mm MTG FS LENS W 110VAC
512-997-76	12.7mm MTG FS LENS W 230VAC
512-997-76-15	12.7mm MTG FS LENS W 230VAC