

TECHNICAL DATA SHEET

Part#: 9246SL

Cutters - Medium Taper Relieved Head -★★★★- Carbon Steel - Slim Line - Black Oxide Coated

The 9246SL five star Lazer Line[®] medium tapered/relieved semi-flush cutter has a cutting capacity of .008" - .036" soft wire. It is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. The CNC machining allows the joint surfaces to be perfect to allow for long life. The dual leaf springs provide smooth action.

- | | |
|-----------------------|--|
| • Precision Level | ★★★★ |
| • Material | Carbon |
| • Surface Resistivity | 10 ¹⁰ ohms/sq |
| • Shape | Taper Relieved Head |
| • Type of Cut | Semi-Flush |
| • Group | Cutting Tools |
| • Cutting Capacity | 32 - 19 AWG / .008" - .036" / .2 - .9 mm |
| • Blade Angle | 16° |
| • Blade Length | .278" (6.95mm) |
| • Body Width | 0.375" (9.38mm) |
| • Body Height | .225" (5.63mm) |
| • OAL | 4.5" (112.5mm) |
| • Weight (OZ) | 3 |
| • UPC | 662847014079 |
| • Schedule B | 8203.20.60.60 |
| • ECCN | EAR99 |
| • UNSPSC Code | 27111511 |
| • Country of Origin | USA |

