

TECHNICAL DATA SHEET

Part#: 9245SL

Cutters - Medium Taper Head - ★★★★★ - Carbon Steel - Slim Line - Black Oxide Coated

The 9245SL five star Lazer Line[®] medium tapered optimum flush cutter has a cutting capacity of .001" - .032" soft wire. It is made of carbon tool steel with induction hardened cutting blades to RHC 63-65. The CNC machining allows the joint surfaces to be perfect to allow for long life. The dual leaf springs provide smooth action.

- Precision Level ★★★★★
- Material Carbon
- Surface Resistivity 10^{10} ohms/sq
- Shape Taper Head
- Type of Cut Lazer Flush
- Group Cutting Tools
- Cutting Capacity 50 - 20 AWG / .001 - .032" / .03 - .88 mm
- Blade Angle 16°
- Blade Length .278" (6.95mm)
- Body Width 0.375" (9.38mm)
- Body Height .225" (5.63mm)
- OAL 4.5" (112.5mm)
- Weight (OZ) 3
- UPC 662847014062
- Schedule B 8203.20.60.60
- ECCN EAR99
- UNSPSC Code 27111511
- Country of Origin USA

