

PRODUCT-DETAILS

TYL300MX

CABLE TIE 250LB 12IN BLK NYL RLSBLE



General Information

Extended Product Type	TYL300MX
Product ID	7TCG054360R0354
EAN	5414363067559
Catalog Description	CABLE TIE 250LB 12IN BLK NYL RLSBLE
Long Description	Heavy Duty Releasable Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Releasable and Reusable, Length of 300mm (11.81 Inches), Width of 13.2mm (0.519 Inches), Tensile Strength Rating of 1120 Newtons (250 Pounds)

Ordering

EAN	5414363067559
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.019 lb 8.617 g
--------------------	--------------------

Container Information

Package Level 1 Units	50 piece
Package Level 2 Units	1000 piece

Package Level 2 Width	10.2 in 259 mm
Package Level 2 Height	13.8 in 351 mm
Package Level 2 Depth / Length	19.7 in 500 mm

Additional Information

Brand / Label	Ty-Fast
Bundle Diameter	2.95 in 75 mm
Color	Black
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	PLASTIC CABLE TIE
Product Type	Releaseable
Tensile Strength	50 lb 222 N
UPC	786210497693

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TYL300MX
Instructions and Manuals	TYL300MX

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

