

Driver Board – Samotronic 101

SAMOTRONIC101

Driver	for unipolar motors
Dimensions (mm)	55 x 40
Supply voltage (VDC)	10-24
Motor current	constant voltage drive
Step mode	full/half step
Clock source	internal or external
Control inputs to	<ul style="list-style-type: none"> ■ inhibit internal clock ■ inhibit motor current ■ exchange direction
Configuration	via DIP-switch



Preferred Range

Ordering Reference

4 636 6608 0 If motors are ordered for please order "with MTA-100 receptacles for use with SAMOTRONIC101".

Technical Data

Supply voltage	10-24 VDC
Phase current	≤ 350 mA
Control signal level	LS-TTL (0-5V) for all control inputs
Internal clock	50-300 Hz
External clock	up to 2 kHz
Dimensions	55 x 40 mm
Operating temperature	-15 to +50 °C
Storage temperature	-20 to +80 °C

Dimensions (mm)

