

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0987891208](#)
Status: **Active**
Description: NSCC Single Part, Non-Sealed, 1.50mm, Male Housing, 10 Circuits, Dual Row, Gray

Documents:

Drawing (PDF)	Application Specification AS-98788-003-001 (PDF)
Application Specification 987880002-AS-CH-001 (PDF)	Application Specification AS-98788-003-FR (PDF)
Application Specification 987880003-AS-CH-001 (PDF)	Packaging Specification PK-98789-001 (PDF)
Application Specification AS-98788-002-001 (PDF)	RoHS Certificate of Compliance (PDF)

Application tooling part link

Application Tooling Part Link 63813-5700

General

Product Family	Crimp Housings
Series	98789
Application	Power, Wire-to-Wire
Product Name	NSCC
UPC	822350007146

Physical

Circuits (maximum)	10
Circuits Detail	10
Color - Resin	Gray
Gender	Plug
Glow-Wire Capable	No
Lock to Mating Part	Yes
Net Weight	11.470/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.25mm
Pitch - Termination Interface	6.00mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +120°C

Electrical

Current - Maximum per Contact	6.0A
-------------------------------	------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	09218EV10F8
--------------------	-------------

Reference - Drawing Numbers

Application Specification	987880002-AS-CH-001, 987880003-AS-CH-001, AS-98788-002-001, AS-98788-003-001, AS-98788-003-FR
Packaging Specification	PK-98789-001
Sales Drawing	SD-98789-003



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[98789](#) Series

Mates With

[98788-1208](#) NSCC Single Non Sealed Male Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extractor Tool for CTX64 Female Crimp Terminals	638135700

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION